

## Fabric – Dip – Rubber standard specifications, others on request

Polyester	NR/SBR	PG02 R152-18G
Polyester	Neoprene	PG02 R252-18G
Polyester	Nitrile	PG02 R352-18G
Polyester	peroxide EPDM	PG02 R520-18G
Polyester	peroxide Silicone	PS15
Para-Aramid	NR/SBR	PG01 R152-18
Para-Aramid	Neoprene	PG01 R252-18
Para-Aramid	Nitrile	PG01 R352-18
Para-Aramid	peroxide EPDM	PG01 R520-18
Meta-Aramid	peroxide Silicone	PA115
Nylon	NR/SBR	R118-15
Nylon	Neoprene	R211-15
Nylon	Nitrile	R311-15
Nylon	peroxide EPDM	R520-18

Sample lengths of dipped fabric are often held in stock for quick despatch for lab testing.

